

Acquista un UPS o un prodotto Avocent presente in questa lista ed entro il 30 settembre potrai acquistare anche i Rack con **un ulteriore 8% di sconto** e/o le PDU con **un ulteriore 10% di sconto** rispetto al prezzo promo.

Codice	Descrizione	Prezzo listino	PROMO Reseller	Sconto applicato
UPS				
PSP500MT3-230U	Liebert® PSP 500VA (300W) 230V UPS	€ 88,00	€ 49,74	43%
PSP650MT3-230U	Liebert PSP 650VA (390W) 230V UPS	€ 123,00	€ 69,52	43%
PSA500MT3-230U	Liebert® PSA 500VA (300W) 230V UPS	€ 138,00	€ 52,50	62%
PSA650MT3-230U	Liebert PSA 650VA (390W) 230V UPS	€ 165,00	€ 59,18	64%
PSA1000MT3-230U	Liebert PSA 1000VA (600W) 230V UPS	€ 264,00	€ 149,22	43%
PSA1500MT3-230U	Liebert PSA 1500VA (900W) 230V UPS	€ 314,00	€ 177,48	43%
LI32101CT00	Liebert itON™ 400VA	€ 125,00	€ 50,27	60%
LI32111CT00	Liebert itON 600VA	€ 148,00	€ 59,52	60%
LI32121CT00	Liebert itON 800VA	€ 187,00	€ 75,21	60%
LI32131CT20	Liebert itON 1000VA	€ 239,00	€ 96,12	60%
LI32141CT20	Liebert itON 1500VA	€ 282,00	€ 122,61	57%
LI32151CT20	Liebert itON 2000VA	€ 336,00	€ 146,09	57%
Edge-750IMT	Edge UPS 750VA 230V Tower	€ 420,00	€ 210,00	50%
Edge-1000IMT	Edge UPS 1kVA 230V Tower	€ 513,00	€ 278,80	46%
Edge-1500IMT	Edge UPS 1.5kVA 230V Tower	€ 766,00	€ 325,76	57%
Edge-500IRM1U	Edge UPS UPS 500VA 230V 1U Rack	€ 516,00	€ 308,48	40%
Edge-1000IRM1U	Edge UPS UPS 1kVA 230V 1U Rack	€ 687,00	€ 373,37	46%
Edge-1500IRM1U	Edge UPS UPS 1,5kVA 230V 1U Rack	€ 1,029,00	€ 559,24	46%
Edge-1500IRT2UXL	Edge UPS UPS 1,5kVA 230V 2U Rack/Tower	€ 766,00	€ 416,30	46%
Edge-2200IRT2UXL	Edge UPS UPS 2,2kVA 230V 2U Rack/Tower	€ 1,123,00	€ 610,33	46%
Edge-3000IRT2UXL	Edge UPS UPS 3kVA 230V 2U Rack/Tower	€ 1,531,00	€ 832,07	46%
Edge-3000IRT3UXL	Edge UPS UPS 3kVA 230V 3U Rack/Tower	€ 1,531,00	€ 832,07	46%
GXTRT-1000IRT2UXL	Vertiv™ GXT RT+ 1ph UPS, 1kVA, input plug IEC60320 C14, 2U, output - 230V, output socket groups (6)C13	€ 708,00	€ 384,78	46%
GXTRT-1500IRT2UXL	Vertiv GXT RT+ 1ph UPS, 1,5kVA, input plug IEC60320 C14, 2U, output - 230V, output socket groups (6)C13	€ 938,00	€ 509,78	46%
GXTRT-2000IRT2UXL	Vertiv GXT RT+ 1ph UPS, 2kVA, input plug IEC60320 C14, 2U, output - 230V, output socket groups (6)C13	€ 1,253,00	€ 680,98	46%
GXTRT-3000IRT2UXL	Vertiv GXT RT+ 1ph UPS, 3kVA, input plug IEC60320 C20, 2U, output - 230V, output socket groups (6)C13 (1)C19	€ 1,668,00	€ 906,52	46%
GXTRT-EBC24VRT2U	Vertiv GXT RT+ external battery cabinet for GXTRT-1000IRT2UXL	€ 438,00	€ 261,85	40%
GXTRT-EBC36VRT2U	Vertiv GXT RT+ external battery cabinet for GXTRT-1500IRT2UXL	€ 516,00	€ 308,48	40%
GXTRT-EBC48VRT2U	Vertiv GXT RT+ external battery cabinet for GXTRT-2000IRT2UXL	€ 603,00	€ 360,49	40%
GXTRT-EBC72VRT2U	Vertiv GXT RT+ external battery cabinet for GXTRT-3000IRT2UXL	€ 778,00	€ 465,11	40%
RMKIT18-32	Liebert® GXT rack slide kits - 18/32"	€ 106,00	€ 57,61	46%
IS-UNITY-SNMP	Liebert Intellislot SNMP WEB Card for Liebert GXT3/GXT4	€ 285,00	€ 154,89	46%
RDU101	INTELLISLOT COMMS CARD	€ 363,00	€ 197,28	46%
LI38000B010	Liebert® Intellislot Relay Card for GXT-MT+	€ 107,00	€ 61,64	42%
LI34101CT32	Liebert® GXT-MT+ 1kVA G2	€ 750,00	€ 407,61	46%
LI34111CT32	Liebert GXT-MT+ 2kVA G2	€ 1.325,00	€ 720,11	46%
LI34121CT32	Liebert GXT-MT+ 3kVA G2	€ 1.768,00	€ 960,87	46%
LI34141CT32	Liebert GXT-MT+ 6kVA G2	€ 3.343,00	€ 1.816,85	46%
LI34151CT32	Liebert GXT-MT+ 10kVA G2	€ 4.888,00	€ 2.656,52	46%
LI38000B010	Liebert GXT-MT+ / RT+ VFC card	€ 107,00	€ 61,64	42%
LI38000B020	Liebert GXT-MT+ / RT+ SNMP card	€ 139,00	€ 80,08	42%

Codice	Descrizione	Prezzo listino	PROMO Reseller	Sconto applicato	
AVOCENT					
ACS8008MDAC-404	8-Port ACS8000 Console System with dual AC Power Supply and Analog Modem	€ 2.521,00	€ 1.452,32	42%	
ACS8016DAC-404	16-Port ACS8000 Console System with dual AC Power Supply	€ 3.006,00	€ 1.731,72	42%	
ACS8016MDAC-404	16-Port ACS8000 Console System with dual AC Power Supply and Analog Modem	€ 3.201,00	€ 1.844,05	42%	
ACS8032MDAC-404	32-Port ACS8000 Console System with dual AC Power Supply and Analog Modem	€ 3.684,00	€ 2.122,30	42%	
ACS8048DAC-404	48-Port ACS8000 Console System with dual AC Power Supply	€ 4.894,00	€ 2.819,37	42%	
ACS8048MDAC-404	48-Port ACS8000 Console System with dual AC Power Supply and Analog Modem	€ 4.957,00	€ 2.855,66	42%	
ACS8008-EU-DAC-400	8 Port ACS8000 cellular with 4G/LTE dual AC Power Supply	€ 3.550,00	€ 2.045,11	42%	
ACS8016-EU-DAC-400	16 Port ACS8000 cellular with 4G/LTE dual AC AC Power Supply	€ 4.306,00	€ 2.480,63	42%	
LRA185KMM-001	19" LCD, USB KB, 2USB PASS-US INTL ENG	€ 1.154,00	€ 664,80	42%	
LRA185KMM8D-001	LCD,8P KVM, 8 CABLES, USB KB-US INTL	€ 1.772,00	€ 1.020,83	42%	
LRA185KMM16D-001	LCD,16P KVM, 16 CABLES, USB KB-US INTL	€ 2.212,00	€ 1.274,30	42%	
Codice	Descrizione	Prezzo listino	PROMO Reseller	Sconto applicato	Ulteriore 8% di sconto
RACK					
VR3100	Rack 42U 1998mm (78,6")H x 600mm (23,62")W x 1115mm (43,89")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 1.382,00	€ 796,15	42%	€ 732,46
VR3300	Rack 42U 1998mm (78,6")H x 600mm (23,62")W x 1215mm (47,83")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 1.696,00	€ 977,04	42%	€ 898,88
VR3150	Rack 42U 1998mm (1998")H x 800mm (31,50")W x 1115mm (43,89")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 1.708,00	€ 983,96	42%	€ 905,24
VR3350	Rack 42U 1998mm (78,6")H x 800mm (31,50")W x 1215mm (47,83")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 2.228,00	€ 1.283,52	42%	€ 1.180,84
VR3107	Rack 48U 2265mm (96,16")H x 600mm (23,62")W x 1115mm (43,89")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 1.638,00	€ 943,63	42%	€ 868,14
VR3307	Rack 48U 2265mm (96,16")H x 600mm (23,62")W x 1215mm (47,83")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 2.102,00	€ 1.210,93	42%	€ 1.114,06
VR3157	Rack 48U 2265mm (96,16")H x 800mm (31,50")W x 1115mm (43,89")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 2.042,00	€ 1.176,37	42%	€ 1.082,26
VR3357	Rack 48U 2265mm (96,16")H x 800mm (31,50")W x 1215mm (47,83")D with (1) 77% Perforated Locking Front Door, (2) 77% Perforated Split Locking Rear Doors, (2) pair 19" Mounting Rails,(4)Split Side Panels with locking slam latch, Toolless Removeable Top Panel, Casters and Leveling Feet, (2) Full Height PDU/Cable Mgt Brackets, (1) Baying Kit, (50) M6 Cage Nuts and Screws, Color RAL 7021 Black gray	€ 2.582,00	€ 1.487,46	42%	€ 1.368,46

Codice	Descrizione	Prezzo listino	PROMO Reseller	Sconto applicato	Ulteriore 10% di sconto
PDU					
VP7551	Vertiv™ Geist™ rPDU, basic, 0U, input IEC60309 230V 16A, outputs (20)C13 (4)C19	€ 276,00	€ 159,00	42%	€ 143,10
VP7552	Vertiv Geist rPDU, basic, 0U, input C20 230V 16A, outputs (20)C13 (4)C19	€ 292,00	€ 168,22	42%	€ 151,40
VP7553	Vertiv Geist rPDU, basic, 0U, input IEC60309 230V 32A, outputs (20)C13 (4)C19	€ 330,00	€ 190,11	42%	€ 171,10
VP7557	Vertiv Geist rPDU, basic, 0U, input IEC60309 230/400V 3x16A, outputs (36)C13 (6)C19	€ 602,00	€ 346,80	42%	€ 312,12
VP8853	Vertiv Geist rPDU, monitored, 0U, input IEC60309 230V 32A, outputs (36)C13 (6)C19	€ 654,00	€ 376,76	42%	€ 339,08
VP8858	Vertiv Geist rPDU, monitored, 0U, input C20 230V 16A, outputs (18)C13 (2)C19	€ 570,00	€ 328,37	42%	€ 295,53
VP8881	Vertiv Geist rPDU, monitored, 0U, input IEC60309 230/400V 3x16A, outputs (36)C13 (6)C19	€ 851,00	€ 490,25	42%	€ 441,23
VP8886	Vertiv Geist rPDU, monitored, 0U, input IEC60309 230/400V 3x32A, outputs (30)C13 (12)C19	€ 1.447,00	€ 833,60	42%	€ 750,24
VP8953	Vertiv Geist rPDU, switched, 0U, input IEC60309 230V 32A, outputs (20)C13 (4)C19	€ 1.183,00	€ 681,51	42%	€ 613,36
VP8959EU3	Vertiv Geist rPDU, switched, 0U, input C20 230V 16A, outputs (21)C13 (3)C19	€ 1.073,00	€ 618,14	42%	€ 556,33
VP9559	Vertiv Geist rPDU, basic, 1U, input C20 230V 16A, outputs (10)C13 (2)C19	€ 265,00	€ 152,66	42%	€ 137,40
VP52101	Vertiv™ Geist™ Rack PDU, Switched (Unit Level), EC, 1U, input IEC 60320 C20 power inlet 230V 16A, combi outputs (12)C13 or C19	€ 827,00	€ 476,42	42%	€ 428,78
VP59100	Vertiv Geist Rack PDU, Switched (Unit Level), EC, 1U, input IEC 60309 230V 32A, combi outputs (12)C13 or C19	€ 950,00	€ 547,28	42%	€ 492,55
VP43903	Vertiv Geist Rack PDU, Monitored (Unit Level), EC, 0U, input IEC 60309 230V 32A, combi outputs (36)C13 or C19	€ 671,00	€ 386,55	42%	€ 347,90
UI30023	Vertiv Geist Rack PDU, Monitored (Unit Level), EC, 0U, UPDU rating 3ph 16A 230/415V, combi outputs (42)C13 or C19	€ 1.053,00	€ 606,62	42%	€ 545,96
UI30024	Vertiv Geist Rack PDU, Monitored (Unit Level), EC, 1U, UPDU rating 3ph 16A 230/415V, combi outputs (12)C13 or C19	€ 865,00	€ 498,32	42%	€ 448,48
FSC1U001	Vertiv™ Geist™ FSC, 1ph/7,3kW, 32A, 230V	€ 158,00	€ 91,02	42%	€ 81,92